

## Designed for Extreme Environments:

We deliver Race Winning Motion Control technology, not just to F1 but other high-performance applications which often involve extreme, challenging environments and specifications.

**Efficiency and Speed:** The E245-100 is designed for precision, efficiency, and durability. It offers resistance to hydraulic contamination, crucial in high-performance applications.

**Lightweight and Compact:** The E245-100 is a compact design that offers a 50% reduction in weight compared to the E242, while still delivering a flow of up to 10 l/min.

Advanced Technology: The E245-100 features Moog's proportional Direct Drive Valve (DDV) technology, which uses a compact and powerful linear force motor to precisely actuate the flow control spool. This technology combines the robust functionality of a proportional valve with the speed and accuracy of a servo valve.

**Optimized Design:** The compact cartridge construction allows for neat integration within a manifold or actuator assembly, particularly within multi-axis systems.

**Power Density:** With a compact and lightweight design, the E245-100 continues to deliver power density where it matters the most.

#### **BENEFITS**

- + Rated flow\*\* range from **0.5 lpm** up to **8.5 lpm** meeting the demands of miniature hydraulic applications
- + High flow capability up to 10 l/min\*
- + Low weight 185 gm
- + High bandwidth for fast accurate control
- + Custom cartridge design for integration into compact manifold
- + Highly resistant to hydraulic contamination
- + Withstands challenging and extreme environments
- + High hydraulic system efficiency. Internal leakage < 0.05 l/min
- + Highly precise linear flow characteristics
- + Withstands high vibration survivability up to 50G

### **INDUSTRY APPLICATIONS**

- Motorsport
- High performance automotive
- Oil & gas exploration
- Medical prosthetics
- High performance marine (including racing yachts)

The new E245-100 has just 42% of the mass of the E242.



- \* With ∆p 210 bar
- \*\* With ∆p 70 bar



Shaping the way our world moves<sup>TM</sup>

## **SPECIFICATIONS**

#### TYPICAL TECHNICAL DATA E245-100 CARTRIDGE DDV PROPORTIONAL VALVE

Max Supply Pressure:	280 Bar			
Rated Flow (Qr): (See below tabulated data for standard flow rates)	Rated flow Qr is specified at 70 bar supply pressure and 4 port connected. Consult Moog for details of flow rates at other pressures and operating modes			
Leakage Flow (Ql): @ 140 Bar with 25 cSt Fluid	P>R port spool null leakages at 140 bar supply (for all models apart from 0.5 lpm rated flow models) is <0.05 lpm. For 0.5 lpm rated flow models leakage at 140 bar supply pressure is <0.025 lpm			
Operating Fluids:	Mineral oil. Consult Moog for other fluid types			
Electrical Input Signal:	trical Input Signal: +/- 1.0A into a 5.7 Ohm, 0.04H load			
Dynamic Performance at 25% signal:	-1.5 dB (bandwidth) 150Hz, 90° phase lag 400 Hz (typical) Mechanical natural frequency and damping ratio 540Hz, 0.2 (typical)			
Accuracy of Flow Control:	Full amplitude Hysteresis <180 mA Threshold <75 mA			
Operational/Environmental Survivability Limits:	Thermal and Shock: 120 °C (248 °F)[TBC] & 25 G shock load (Any axis) [TBC] Corrosion Resistance: 240 hours to ASTM B117 Salt Spray Test.			
Connector Type:	Flying lead: PTFE insulated 24 AWG copper wire lead length 350 mm			
Mass:	185 gm			

#### TWO BASIC VERSIONS OF THE E245 PROPORTIONAL VALVE ARE AVAILABLE:



An axis-cut (Q) version for use in position, pressure and force control applications




A switching version which is designed for applications that require fast directional control such as gear shift actuation.

#### FLOW CONTROL VALVE STANDARD MODEL NUMBERS

Bias (%)	E245-100 Series, Flow Control Standard Axis Cut Valves Rated flow @ 70 bar, 4 port connected (I/min)						
	0.5	1.5	2.5	5.5	8.5		
None 0 %	E245-101	E245-102	E245-103	E245-104	E245-105		
P>A 15%	E245-106	E245-107	E245-108	E245-109	E245-110		
P>B 15%	E245-111	E245-112	E245-113	E245-114	E245-115		

# TYPICAL GENERAL INSTALLATION INFORMATION




#### **Electrical connections:**

Polarity: +ve signal to White lead gives flow out of port A



For full installation information see drawing number CD25658

#### Hydraulic Schematic:



#### SHIFT VALVE STANDARD MODEL NUMBERS

Bias (%)	E245-100 Series, Switching Standard Valves Rated flow rates @ 70 bar, 4 port connected (I/min)				Note  Both Option A & B shift valves have control ports which are connected	
	A- 30% OLP, 30%	6 ULR	B- 30% OLP, 60%	S ULR	to return pressure at zero signal.  Option A has both return lands open until 30% signal and the pressure	
None 0 %	4.5	7.0	4.5	7.0	lands closing until 30% signal.	
	E245-116	E245-117	E245-118	E245-119	Option B has both return lands open until 60% signal and the pressure land closing at 30% signal.	

# For further information, visit:

www.moog.com/miniature

This technical data is based on current available information and is subject to change at anytime by Moog. Performance for specific systems or applications may vary.

Moog is a registered trademark of Moog Inc. and its subsidiaries. All trademarks as indicated herein are the property of Moog Inc. and its subsidiaries. @04/2024 Moog Inc. All rights reserved. All changes are reserved. CDL-67100



SHAPING THE WAY OUR WORLD MOVES TM

Moog Industrial Group.

Ashchurch Parkway, Tewkesbury, Glos. GL20 8TU UK

Tel: +44 (0)1684 858000